

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2451350220](#)
Status: **Active**
Overview: [Mini-Fit Jr. Power Connectors](#)
Description: Mini-Fit Jr.-to-Mini-Fit Jr. Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, 2.0m Length, 2 Circuits, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification 245135022-PK \(PDF\)](#) [Product Literature \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	245135
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Mini-Fit Jr. Both Ends
Overmolded	Yes
Overview	Mini-Fit Jr. Power Connectors
Product Literature Order No	987650-3291
Product Name	Mini-Fit Jr.
Type	Overmolded Assembly
UPC	889056862141

Physical

Cable Length	2.0m
Circuits (Loaded)	2
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	100.100/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	4.20mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	5.40mm
Wire Size AWG	18
Wire/Cable Type	UL 2464


Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	300V AC

Material Info

Reference - Drawing Numbers

Packaging Specification	245135022-PK
Sales Drawing	2014400029-000



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[245135](#) Series

Mates With

Dual Row Plug Housing [5559](#)
Dual Row Header [5566](#) , [5569](#) , [87427](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION