

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2451350820](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit Jr. Power Connectors](#)  
**Description:** Mini-Fit Jr.-to-Mini-Fit Jr. Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, 2.0m Length, 8 Circuits, Black

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification 2027040005-PK \(PDF\)](#) [Product Literature \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">245135</a>
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Mini-Fit Jr. Both Ends
Overmolded	Yes
Overview	<a href="#">Mini-Fit Jr. Power Connectors</a>
Product Literature Order No	987650-3291
Product Name	Mini-Fit Jr.
Type	Overmolded Assembly
UPC	889056879637

**Physical**

Cable Length	2.0m
Circuits (Loaded)	8
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	248.000/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	4.20mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	5.40mm
Wire Size AWG	18
Wire/Cable Type	UL 2464


**Electrical**

Current - Maximum per Contact	6.0A
Voltage - Maximum	300V AC

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	2027040005-PK
Sales Drawing	2014400058-000



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[245135 Series](#)

**Mates With**

Dual Row Plug Housing [5559](#) <br>Dual Row Header [5566](#) , [5569](#) , [87427](#)

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**