

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0340620028](#)
Status: **Active**
Overview: [MX150™ Sealed and Unsealed Connector System](#)
Description: MX150™ Sealed Female Receptacle, Single Row, 2 Circuits, Keying Option D, with CPA, without Clip Slot, Black

Documents:

3D Model	Application Specification AS-34062-000-001 (PDF)
Drawing (PDF)	Packaging Specification PK-30907-879 (PDF)
Product Specification PS-34062-000-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification TS-34062-992-001 (PDF)	



General

Product Family	Crimp Housings
Series	34062
Application	Power
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications-Partnership
Overview	MX150™ Sealed and Unsealed Connector System
Product Name	MX150™
UPC	883906212278

Physical

Circuits (maximum)	2
Color - Resin	Black
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	4.400/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.00mm
Pitch - Termination Interface	5.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-34062-000-001
Packaging Specification	PK-30907-879
Product Specification	PS-34062-000-001, TS-34062-992-001
Sales Drawing	SD-34062-002-000, SD-34062-004-001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[34062](#) Series

Mates With

[34675](#) MX150™ Cable-Sealed Male Connector

Use With

[34083](#) Tin (Sn) Cable Seal Female Terminal,
[34081](#) Silver (Ag) and Gold (Au) Cable Seal Female Terminal