

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0847290004**
Status: **Active**
Overview: Sealed Industrial USB Solutions
Description: Sealed Industrial USB 2.0 Type A Plug-to-USB 2.0 Type A Receptacle, 28 AWG, 0.80M Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-84727-002-001 \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	84729
Assembly Configuration	Dual Ended Connectors
Comments	Fully shielded for EMI/RFI protection
Connector to Connector	Type A Recept-to-Type A Plug
Overview	Sealed Industrial USB Solutions
Product Name	Industrial USB
UPC	822348832002

Physical

Cable Length	0.80m
Circuits (Loaded)	4
Color - Resin	Black
Gender	Female-Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	PBT
Packaging Type	Bag
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Single Ended	No
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67, NEMA 6P
Wire Size AWG	28
Wire/Cable Type	USB

Electrical

Current - Maximum per Contact	1.0A
Impedance	90Ω
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC (RMS)

Material Info

Reference - Drawing Numbers

Product Specification	PS-84727-002-001
Sales Drawing	SD-84729-006



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

84729 Series

Mates With

Industry Standard Bayonet Locking USB Type A Plug and Industry Standard USB Type A Receptacle