

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0191930103**
Status: **Active**
Overview: VersaKrimp™ Terminals and Splices
Description: VersaKrimp™ Ring Tongue Terminal for 10-12 AWG Wire

Documents:

Drawing (PDF) Product Specification PS-19902-013-001 (PDF)
Product Specification PS-19902-011-001 (PDF) RoHS Certificate of Compliance (PDF)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Ring and Spade Terminals
 Series 19193
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview VersaKrimp™ Terminals and Splices
 Product Name VersaKrimp™
 Type Ring
 UPC 800755049404

Physical


Barrel Type Closed - Brazed
 Insulation None
 Material - Plating Mating Tin
 Net Weight 1.560/g
 Packaging Type Bag
 Stud Size 5-6 (M3-3.5)
 Wire Size AWG 10, 12
 Wire Size mm² 3.30-5.00

Material Info

Engineering Number C-328-06

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-013-001
 Sales Drawing SD-19193-023



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
 ED/108/2014 (17 Dec
 2014)

Boric acid

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19193 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION