

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008500160](#)
Status: **Active**
Overview: KK® Interconnect System - Molex
Description: KK® 254 Crimp Terminal, 22-30 AWG, Bag, Tin (Sn) Plating, Nickel (Ni) Under Plating

Documents:

Drawing (PDF) Packaging Specification PK-2759-001 (PDF)
Product Specification PS-10-07-001 (PDF) RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	<u>2759</u>
Application	Signal
Crimp Quality Equipment	Yes
Overview	<u>KK® Interconnect System - Molex</u>
Product Name	KK® 254
UPC	800754224710

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.068/g
Packaging Type	Bag
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.57mm max.
Wire Size AWG	22, 24, 26, 28, 30
Wire Size mm²	N/A

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	2759-(154)L
--------------------	-------------

Reference - Drawing Numbers

Packaging Specification	PK-2759-001
Product Specification	PS-10-07-001
Sales Drawing	SD-2759



EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

2759 Series

Use With

2695 , 5051

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION