

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0458440004](#)
Status: **Active**
Overview: Edge Card Connectors
Description: 2.50mm Pitch EXTreme PowerEdge™, Signal Connector, Double Sided, 2 Segments Thick PC Board

Documents:

[3D Model](#) [Packaging Specification PK-45714-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Edge Card Connectors
 Series 45844
 Circuit Size Range 1-64 Circuits
 Component Type Edgcard to PCB
 Data Rate Unrated
 Edge Card Thickness 1.57mm
 High Power Bay (30.0A or more) No
 Orientation Vertical
 Overview [Edge Card Connectors](#)
 Product Name EXTreme PowerEdge™
 Standard Based General
 UPC 822350205610

Physical


(p)ower-(s)ignal Configuration 16s - 0p
 Circuits (Loaded) 16
 Circuits (maximum) 16
 Color - Resin Black
 Durability (mating cycles max) 250
 Entry Angle Vertical (Top Entry)
 Flammability 94V-0
 Keying to Mating Part N/A
 Material - Metal Phosphor Bronze
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Material - Resin High Temperature Thermoplastic
 Net Weight 3.270/g
 PC Tail Length 3.19mm
 PCB Thickness - Recommended 1.60mm
 Packaging Type Tray
 Pitch - Mating Interface 2.50mm
 Plating min - Mating 0.762µm
 Plating min - Termination 3.810µm
 Temperature Range - Operating -40°C to +105°C
 Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 3.0A
 Voltage - Maximum 250V

Solder Process Data

Duration at Max. Process Temperature (seconds) 005
 Lead-freeProcess Capability WAVE



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/01/2017 (12
 January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

45844 Series

Mates With

1.58mm Double Sided Card Edge

Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	245

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-45714-001
Sales Drawing	SD-45844-001, SD-45844-002

This document was generated on 07/26/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION