

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0847271005](#)
Status: **Active**
Overview: [Sealed Industrial USB Solutions](#)
Description: Sealed Industrial USB Type A Plug-to-Shielded Pigtail, 0.15m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-84727-002-001 \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	84727
Assembly Configuration	Single Ended Connector
Comments	Fully shielded for EMI/RFI protection
Connector to Connector	USB Type A-to-Pigtail
MolexKits	Yes
Overview	Sealed Industrial USB Solutions
Product Name	Industrial USB
UPC	822350041119

Physical

Cable Length	0.15m
Circuits (Loaded)	5
Color - Resin	Black
Gender	Plug
Lock to Mating Part	None
Material - Resin	Polyester, PVC
Packaging Type	Bag
Pitch - Mating Interface	2.00mm, 2.50mm
Single Ended	Yes
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67
Wire Insulation Diameter	N/A
Wire Size AWG	N/A
Wire/Cable Type	USB

Electrical

Current - Maximum per Contact	1.0A
Impedance	Non-constant
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC (RMS)

Material Info

Reference - Drawing Numbers

Product Specification	PS-84727-002-001
Sales Drawing	SD-84727-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
ED/108/2014 (17 Dec
2014)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Contained: DEHP

Search Parts in this Series

[84727 Series](#)

Mates With

[84729 Sealed Industrial USB 2.0 Type A Panel Mount PCB Receptacle](#)