

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0002081003](#)
Status: **Active**
Overview: [MLX™ Power Connectors](#)
Description: [MLX™ Female Crimp Terminal 42024, 14-20 AWG, Reel, Phosphor Bronze, Tin \(Sn\) Plating](#)

Documents:

[3D Model](#) [Product Specification TS-42022-0001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-42022-0001-001 \(PDF\)](#)

General

Product Family [Crimp Terminals](#)
Series [42024](#)
Application [Power](#)
Crimp Quality Equipment [Yes](#)
Overview [MLX™ Power Connectors](#)
Packaging Alternative [02-08-1004 \(Loose\)](#)
Product Name [MLX™](#)
UPC [800753618411](#)

Physical

Gender [Female](#)
Material - Metal [Phosphor Bronze](#)
Material - Plating Mating [Tin](#)
Material - Plating Termination [Tin](#)
Net Weight [0.359/g](#)
Packaging Type [Reel](#)
Plating min - Mating [0.508µm](#)
Plating min - Termination [0.508µm](#)
Termination Interface: Style [Crimp or Compression](#)
Wire Insulation Diameter [1.52-3.30mm](#)
Wire Size AWG [14, 16, 18, 20](#)
Wire Size mm² [N/A](#)

Solder Process Data

Lead-freeProcess Capability [N/A](#)

Material Info

Engineering Number [42024-1B1](#)

Reference - Drawing Numbers

Product Specification [PS-42022-0001-001, TS-42022-0001-001](#)
Sales Drawing [SD-42024-****](#)



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[42024 Series](#)