

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0192030148](#)  
**Status:** **Active**  
**Overview:** [High-Temperature Temp Terms Terminals and Splices](#)  
**Description:** VersaKrimp™ Temp-Term Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 1/4" (M6)

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)  
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series [19203](#)  
 Comments 650° F (343° C)  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview [High-Temperature Temp Terms Terminals and Splices](#)  
 Product Name Temp-Terms, VersaKrimp™  
 Type Ring  
 UPC 800755059649

**Physical**

Barrel Type Closed - Brazed  
 Insulation None  
 Material - Plating Mating Tin  
 Net Weight 1.001/g  
 Packaging Type Bag  
 Stud Size 1/4" (M6)  
 Wire Size AWG 14, 16  
 Wire Size mm² 1.00-2.50

**Material Info**

Engineering Number BB-T-325-14

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001, PS-19902-013-001  
 Sales Drawing BBTCD30101



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Relevant**

**REACH SVHC**

Not Relevant

**Halogen-Free**

**Status**

**Not Relevant**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Relevant

**Search Parts in this Series**

[19203 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**