

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0002061132](#)
Status: **Active**
Overview: Standard .062" Pin and Socket Power Connectors
Description: 1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1855, Female, with Tin (Sn) Plated Brass Contact, 24-30 AWG, Bag

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-1190-003 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	<u>1855</u>
Application	Power
Crimp Quality Equipment	Yes
Overview	<u>Standard .062" Pin and Socket Power Connectors</u>
Packaging Alternative	<u>02-06-1131 (Reel)</u>
Product Name	Standard .062"
UPC	800753616042

Physical


Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.130/g
Packaging Type	Bag
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.02-2.29mm
Wire Size AWG	24, 26, 28, 30
Wire Size mm ²	N/A

Material Info

Engineering Number	1855-(P901)L
--------------------	--------------

Reference - Drawing Numbers

Packaging Specification	PK-1190-003
Sales Drawing	SD-1855-*



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[1855 Series](#)