

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0747521301](#)  
**Status:** **Active**  
**Overview:** SFP+ Passive Cable Assembly  
**Description:** SFP+-to-SFP+ Passive Cable Assembly, 10Gbps, 30 AWG Cable, Pull-to-Release Plunger Style Latch, 3.0m Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E72548

**General**

Product Family Cable Assemblies  
 Series [74752](#)  
 Assembly Configuration Dual Ended Connectors  
 Comments Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths.  
 Connector to Connector SFP Plus-to-SFP Plus  
 Overview [SFP+ Passive Cable Assembly](#)  
 Product Name SFP Plus  
 UPC 800756660851

**Physical**

Cable Length 3.0m  
 Circuits (Loaded) TWO DIFFERENTIAL PAIR  
 Gender Male-Male  
 Lock to Mating Part Yes  
 Material - Metal Beryllium Copper, Zinc Alloy  
 Net Weight 222.788/g  
 Packaging Type Bag  
 Single Ended No  
 Waterproof / Dustproof Yes  
 Wire Insulation Diameter N/A  
 Wire Size AWG 30  
 Wire/Cable Type Twin-ax

**Electrical**

Impedance 100Ω  
 Shield Type Full Shield  
 Shielded Yes  
 Voltage - Maximum 3.3V

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing 747520001-000



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/30/2017 (7 July 2017)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[74752](#) Series

**Mates With**

[74441](#) SFP Plus (SFP+) Host Connector