

## Datasheet for 76650-0048

### General Information

<b>Kit Part Number:</b>	76650-0048
<b>Connector Type:</b>	Wire Management
<b>Solution:</b>	Maintenance, Repair and Operation Connectors
<b>Molex Family:</b>	Solderless Terminals
<b>Certificates:</b>	N/A
<b>Country of Origin:</b>	Kit assembled in U.S.A

### Specifications

<b>Insulation:</b>	Nylon
<b>Mounting Style:</b>	Non-Mounted
<b>Orientation:</b>	Wire Twist Lock Splices
<b>Tool Included:</b>	No
<b>Voltage Rating:</b>	600V
<b>Wire Gauge (AWG):</b>	16-10, 22-10, 22-14

### Product Highlights

Wire connectors offer a cost-effective way to produce safe and secure wire connections. The tough, thermoplastic shell of the Molex® wire connectors provide superior protection against environmental extremes. The fixed square-wire spring construction provides a secure connection that will not relax over time.

#### Features and Benefits

- Thermoplastic shell offers UL 94-V2 flame retardant protection
- Fixed square-wire spring grasps onto wire quickly
- Threaded funnel entry guides wires into the connector
- Deep skirt provides flashover protection
- Twist and Wing Locks are UL listed and CSA Certified
- 600 volt max. (1000 volt max in lighting fixtures and signs)

#### Applications

- General MRO (Maintenance Repair and Operations)
- Junction Boxes
- Lighting Fixtures
- Signs

<http://www.molexkits.com>

**Bill of Materials**

<b>Molex Part No.</b>	<b>Description</b>	<b>Quantity</b>
19160-0039	Gray Wire Twist Lock Splices, 22-14 AWG	40
19160-0040	Blue Wire Twist Lock Splices, 22-14 AWG	20
19160-0041	Orange Wire Twist Lock Splices, 22-14 AWG	15
19160-0042	Yellow Wire Twist Lock Splices, 22-10 AWG	10
19160-0043	Red Wire Twist Lock Splices, 22-8 AWG	10

**Recommended Molex Tool**

<b>Molex Part No.</b>	<b>Description</b>
None	No Additional Information