

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0428160312](#)
Status: **Active**
Overview: Mini-Fit Sr. Power Connectors
Description: 10.00mm Pitch Mini-Fit Sr.™ Receptacle Housing, Single Row, 3 Circuits

Documents:

3D Model	Packaging Specification PK-42816-002-001 (PDF)
Drawing (PDF)	Test Summary TS-42815-001 (PDF)
Product Specification TS-42815-004-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	42816
Application	Power, Wire-to-Board
MolexKits	Yes
Overview	Mini-Fit Sr. Power Connectors
Product Name	Mini-Fit Sr.™
UPC	800754381673

Physical

Circuits (maximum)	3
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	6.459/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	10.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Electrical

Current - Maximum per Contact	50.0A
-------------------------------	-------


Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-42816-002-001
Product Specification	TS-42815-004-001
Test Summary	TS-42815-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[42816](#) Series

Mates With

[42818-0312](#) , [42820](#) 3 Circuit Right Angle
Headers

Use With

Terminal Position Assurance (TPA™) Clip
Included. [42815](#) Female Crimp Terminal