

MATERIALS AND FINISHES

BODY, COUPLING NUT, CRIMP TUBE BRASS  
PLATED NICKEL

CENTER CONTACT BERYLLIUM COPPER  
PLATED GOLD

OUTER CONTACT BERYLLIUM COPPER  
PLATED NICKEL


INSULATOR TEFLON

SHRINK TUBE ATUM 1/4-0

PROTECTIVE CAP VINYL

CABLE BELDEN 83269

ASSEMBLIES ARE IN  
COMPLIANCE WITH  
IPC-A-620 CLASS 3



PART # 73419-2210

MIL-STD-348A, FIG. 314.2	INTERFACE
SPECIFICATION	DESCRIPTION

CHG: UPDATED CAP. EC NO: URF2011-0373 DRW: ARROBERTSON 2010/12/30 CHKD: SSS 2010/12/30 APPR: JWIENER 2011/01/04	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
		4 PLACES ± --- ± ---	3 PLACES ± --- ± ---	2 PLACES ± --- ± ---	1 PLACE ± --- ± ---	DRAWN BY TEF	DATE 2003/01/03	TITLE CABLE ASSY, SHV PLUG, RA 50 OHMS, BELDEN 83269 EWR-1904, CA-SHV		
		ANGULAR ± 2 °				CHECKED BY SSS	DATE 2003/01/03	APPROVED BY GMH		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				MATERIAL NO. 734192210	DATE 2003/01/03	DOCUMENT NO. SD-73419-221		SHEET NO. 1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										