

[Home](#) >

**Part Number: 170026-9974**

2P CUSTOM INMPACT RAM 10 COL LG

Image not available

Status: Active  
Series: [76450](#)  
Category: Molex Parts

[Go to Part Detail](#)

[CHECK DISTRIBUTOR INVENTORY](#)

[Add to MyParts](#)

Series image - Reference only

**Specifications & Other Documents:**

Documents not available online

Note - Please disable browser pop-up blockers to view documents on [www.molex.com](http://www.molex.com)

**Product Environmental Compliance**

Questions on Product Environmental Compliance? Email [productcompliance@molex.com](mailto:productcompliance@molex.com)

**EU RoHS:** ELV and RoHS Compliant

**China RoHS:**

**REACH SVHC:** Contains SVHC: No

**Low-Halogen Status:** Low-Halogen

[Product Compliance Statement](#)

**Application Tooling**

[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application Tooling**

[Check our list of old tooling that used to be available for this part](#)

**Part Detail**

[COLLAPSE ALL](#)

**General**

Status	Active
Category	Molex Parts
Series	<a href="#">76450</a>
UPC	887191196558

**Physical**

Net Weight	14.505/g
------------	----------

**Material Info**

**Molex Connectors**

Wire-to-Board  
Board-to-Board  
Wire-to-Wire  
Input/Output (IO)  
FFC/FPC  
Sockets

**Other Products**

Fiber Optic Products  
Antennas  
Industrial Automation  
Membrane Switches  
Copper Flex  
PCB Assemblies  
Woodhead Electrical  
Solid State Lighting

**Resources**

Contact Us  
Catalog  
Cross-Reference  
Industries  
Literature  
Product Name

**Company Info**

About Us  
Careers  
ecocare  
Investors  
Press Room  
Shows & Events  
Supplier Portal

**Other Info**

Feedback  
Help  
Legal Disclaimer  
View Mobile Site  
Privacy Policy  
Sitemap

**Stay Connected with Molex:**

