

Home: [Datasheet](#)

Part Number: 87892-1200



Status: Active - Custom
Series: [87892](#)
Category: Molex Parts

[CHECK DISTRIBUTOR INVENTORY](#)

[Add to My Parts](#)

Go to [Part Detail](#)

Questions on Product Environmental Compliance? Email productcompliance@molex.com

[EU RoHS](#) : ELV and RoHS Compliant
[China RoHS](#) :
[REACH SVHC](#) : Contains SVHC: No
[Low-Halogen Status](#) : Low-Halogen

Product Compliance Statement

Application Tooling ♦♦

[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Part Detail

[SHOW ALL](#)

General

Status	Active - Custom
Category	Molex Parts
Series	87892
UPC	822350115087

Physical

Flammability	94V-0
Net Weight	1.883/g

Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number. [Click here to visit the UL Database](#)

CSA	LR19980
UL	E29179

Solder Process Data

Duration at Max. Process Temperature (seconds)	10
Lead-free Process Capability	Reflow Capable (SMT only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	260

Material Info

Molex Connectors

- Wire-to-Board
- Board-to-Board
- Wire-to-Wire
- Input/Output (IO)
- FFC/FPC
- Sockets

Other Products

- Fiber Optic Products
- Antennas
- Industrial Automation
- Membrane Switches
- Copper Flex
- PCB Assemblies

Resources

- Contact Us
- Catalog
- Cross-Reference
- Industries
- Literature
- Product Name

Company Info

- About Us
- Careers
- ecocare
- Investors
- Press Room
- Shows & Events

Other Info

- Feedback
- Help
- Legal Disclaimer
- View Mobile Site
- Privacy Policy
- Sitemap

- Woodhead Electrical
- Solid State Lighting

- Supplier Portal

Stay Connected with Molex:

□□ □
□□□

Copyright 2014