

Home:>

Part Number: 44978-0001

Image not available

Status: Active - Custom
Series: 44978
Category: Molex Parts

[CHECK DISTRIBUTOR INVENTORY](#)

[Add to My Parts](#)

Go to [Part Detail](#) ▼

Series image - Reference only

Specifications & Other Documents:

Documents not available online

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

[EU RoHS](#): ELV and RoHS Compliant

[China RoHS](#):

[REACH SVHC](#): Not Reviewed

[Low-Halogen Status](#): Low-Halogen

[Product Compliance Statement](#)

Application Tooling

[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Part Detail

[COLLAPSE ALL](#)

▼ **General**

Status	Active - Custom
Category	Molex Parts
Series	44978
UPC	800756566849

▼ **Physical**

Net Weight	18.947/g
------------	----------

▼ **Solder Process Data**

Lead-free Process Capability	SMC & Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	235

▼ **Material Info**

Molex Connectors

- Wire-to-Board
- Board-to-Board
- Wire-to-Wire
- Input/Output (IO)
- FFC/FPC
- Sockets

Other Products

- Fiber Optic Products
- Antennas
- Industrial Automation
- Membrane Switches
- Copper Flex
- PCB Assemblies
- Woodhead Electrical
- Solid State Lighting
- Application Tooling

Resources

- Contact Us
- Catalog
- Cross-Reference
- Industries
- Literature
- Product Name

Company Info

- About Us
- Careers
- ecocare
- Investors
- Press Room
- Shows & Events
- Supplier Portal

Other Info

- Feedback
- Help
- Legal Disclaimer
- Trademarks
- View Mobile Site
- Privacy Policy
- Sitemap

Stay Connected with Molex:

