

[PRODUCTS](#)
[Rocker switches](#)
[Pushbutton switches](#)
[Toggle switches](#)
[Slide switches](#)
[Rotary switches](#)
[Foot switches](#)
[Tact and key switches](#)
[Snap-action switches](#)
[Micro-signal switches](#)
[ECO switches](#)
[Sensors](#)
[Push'n'Drive](#)
[Systems and modules](#)
[Accessories](#)
[General information](#)
[Catalog request / download](#)
[PRODUCTS](#) ▶ [ROCKER SWITCHES](#)

## SERIES 1830 - SINGLE AND DOUBLE-POLE ROCKER SWITCHES - TO 20 (4) A 250 V AC

[◀ Show previous product](#)
[Show next product ▶](#)
[1839.1407](#)
[Drawing](#)
[Accessories](#)


Similar to original product

→ [Print data sheet](#)

Product number	1839.1407
Actuator color / printing	
Miscellaneous	momentary function both sides
Switching function	Changeover switch with OFF position in the center (DPDT - Center OFF)
Number of poles	2-pole
connections	Quick-connect terminal, 4.8
Mechanical life endurance	5E4
Rating IEC	6 (4) A 250 V AC 1E4
Rating North America	6 A 125 - 250 V AC 1/8 HP
Contact resistance (new condition)	< 100 (1 A 12 V DC) mOhm
Insulation resistance (new condition)	> 100 (500 V DC) MOhm
Proof tracking	250 PTI
Protection type	Connection IP40
Ambient temperature	-20 °C ... +105 °C
Ambient temperature	-20 °C ... +55 °C
Flammability	UL 94 V-2
Glow wire test temperature	850 °C
Actuators and additional actuators	FA, black
Housing description	FA, black
Connection surface	external connection silver plated
Contact material	Ag
Contact distance	≥ 3 mm
Plug force of the terminals	≤ 80 N
Approval marks	CSA / UL / ENEC 05
Suitable for appliances of protection class	II
Shop / Stock version	