

PRODUCTS

- Rocker switches
- Pushbutton switches
- Toggle switches
- Slide switches
- Rotary switches
- Foot switches
- Tact and key switches**
- Snap-action switches
- Micro-signal switches
- ECO switches
- Sensors
- Systems and modules
- Accessories
- General information
- Catalog request / download

[PRODUCTS](#) ▶ [TACT AND KEY SWITCHES](#)

Tact and key switches

SERIES 6450 - KEY SWITCHES - TO 100 MA 28 V


[Show next product ▶](#)

6450.0001

[Drawing](#)


Similar to original product

[→ Print data sheet](#)

Product number	6450.0001
Actuator color / printing	
Miscellaneous	gray
Switching function	Normally open contact (SPNO)
Number of poles connections	1-pole PCB terminal
Mechanical life endurance	1E6 by 10mA 12V
Rating IEC	100 mA 28 V
Contact resistance (new condition)	< 250 mOhm
Insulation resistance (new condition)	> 100 MOhm
Ambient temperature	-20 °C ... +80 °C
Actuators and additional actuators	PA, gray
Housing description	PBTP
Connection surface	external connection tinned
Contact material	Au
Contact distance	< 3 mm
Operating force	0.7 N
Bounce time	< 5 ms
Total travel / stroke	1.4 ± 0.2 mm
Shop / Stock version	