

## Honeywell Sensing and Control



Search

**115-202CDK-801**

( Home : Products : Sensors » Temperature Sensors » Discrete Thermistors » 115 )

### narrow your search

#### Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6158)
- Switches (9781)
- Wireless (45)

#### Technology

- Control and Instrumentation (890)
- Electromechanical (9303)
- Magnetic (538)
- Platinum thin film (56)
- Thick Film (1372)
- More...

### new products

#### New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site  
WGLA and WPMM  
XYR6000™

[find out more](#)

### white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

### Need help?

[Click here to contact us](#)



*Actual product appearance may vary.*

**115 Series, EI tested and matched beads on header assembly, 2,000 Ohm resistance, ±25.0% tolerance, 25/85 BETA = 3068**

[Sales & Service](#)

[Distributor Inventory](#)

[Overview](#)   [Specs](#)   [Documentation](#)   [Application Notes](#)

#### Product Specifications

Availability	Global
Resistance	2,000 Ohm
Tolerance	±25.0%
Accuracy	25 °C [77 °F]
Beta	3068
Operating Temperature	-60 °C to 300 °C [-76 °F to 572 °F]
Diameter	0,36 mm [0.014 in]
Termination Material	Glass to metal header
Lead Length	9,6 mm [0.375 in]
Time Constant in Air	0.5 s
Dissipation Constant	0,4 m/W°C
Series Name	115

### contacts

Customer Service  
Technical Support  
Global Sales & Service  
View Site Demo  
Site Comments?

### meet dr. larry

**VIDEO** - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

### my links

[Login to iCOM](#)  
[Login to Rep/AD Portal](#)  
[Login to Digital University](#)

### News Center

HONEYWELL INTRODUCES TRUSTABILITY® NSC SERIES, UNCOMPENSATED / UNAMPLIFIED BOARD MOUNT PRESSURE SENSORS

HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER

HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION

**MICRO SWITCH**  
Anniversary site