



HONEYWELL  
PART NUMBER  
11SM1077-H4  
PRODUCT CODE  
TWY2325

REV	DOCUMENT	CHANGED BY	CHECK
4	0038444	KVS 09APR08	ASD



PLASTIC PLUNGER



NOTE

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ±.002 CENTERS
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - SWITCH WILL WITHSTAND A TEMPERATURE OF 250° F
- 4 - MATING CONTACT SURFACES ARE OVERLAYS OF 24K SOLID GOLD AND GOLD ALLOY

RELEASE NO.	PR - 5396
REPLACES	X63185 - SM

CHARACTERISTICS
OPERATING FORCE - - - - 3 - 5 OZ
RELEASE FORCE - - - - 1 OZ MIN
DIFFERENTIAL TRAVEL - - - .004 MAX
OVERTRAVEL - - - - - .005 MIN

ELECTRICAL DATA
CONTACT ARRANGEMENT SPDT

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:
NO PLACE X ±
ONE PLACE .X ±
TWO PLACE .XX ±
THREE PLACE .XXX ±
FOUR PLACE .XXXX ±
ANGLES ±

DRAWN	VK	14 FEB 08
CHECK	RJ	14 FEB 08
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		

<b>Honeywell</b>			
TITLE <b>SWITCH - BASIC</b>			
SIZE	TYPE	DRAWING NAME	REV
<b>B</b>	<b>I</b>	<b>11SM1077-H4</b>	<b>4</b>
SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1

APPROVALS	UL, CSA	0.1A 125 VAC 30 VDC			BRAND	L171
-----------	---------	---------------------	--	--	-------	------

