



HONEYWELL  
PART NUMBER  
11SM2442-T  
PRODUCT CODE  
TWZ2430

REV	DOCUMENT	CHANGED BY	CHECK
5	0038224	KVS 22APR08	ASD



**NOTE -**

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ± .002 CENTERS
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 400° F

RELEASE NO. PR - 8381

REPLACES -

**CHARACTERISTICS**

OPERATING FORCE - - - - 4 OZ MAX

RELEASE FORCE - - - - 1 OZ MIN

DIFFERENTIAL TRAVEL - - - .002 MAX

OVERTRAVEL - - - - .005 MIN

**ELECTRICAL DATA**

CONTACT ARRANGEMENT SPDT

30 VOLTS DC RATING

	SEA LEVEL	50,000 FT
INDUCTIVE	3 AMP	2.5 AMP
RESISTIVE	5 AMP	5 AMP

MAXIMUM INRUSH 24 AMP

APPROVALS: KEMA, CE 5A, 250V ~ T85 1E4, UL, CSA 5A, 250 VAC

DESIGN UNITS: INCH

TOLERANCES UNLESS NOTED:

NO PLACE	X	±	
ONE PLACE	.X	±	0.030
TWO PLACE	.XX	±	0.015
THREE PLACE	.XXX	±	0.005
FOUR PLACE	.XXXX	±	
ANGLES		±	

THIRD ANGLE PROJECTION

DRAWN	VK	27 NOV 07
CHECK	RJ	27 NOV 07

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY

**Honeywell**

TITLE: SWITCH - BASIC

SIZE	TYPE	DRAWING NAME	REV
B	I	11SM2442-T	5

RASTER

SCALE - WEIGHT .006 LB MAX SHEET 1 OF 1

SCALE - WEIGHT .006 LB MAX SHEET 1 OF 1

SCALE - WEIGHT .006 LB MAX SHEET 1 OF 1

SCALE - WEIGHT .006 LB MAX SHEET 1 OF 1