



HONEYWELL PART NUMBER
11SM423-H2
PRODUCT CODE TWY1151

REV	DOCUMENT	CHANGED BY	CHECK
4	0038104	PK 23APR08	ASD



- NOTES**
- ▲-MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375±.002 CENTERS
  - 2-TERMINALS ARE PLATED FOR SOLDERING
  - 3-DEAD BREAK CONDITIONS :  
 A - MAX AMOUNT PERMISSIBLE ----- .0002 IN.
  - 4 - MATING CONTACT SURFACES ARE 24K SOLID GOLD OVERLAY

RELEASE NO.	PR -17956
REPLACES	X90662- SM

**CHARACTERISTICS**

OPERATING FORCE --- 3 1/2 OZ MAX

RELEASE FORCE----- 1 OZ MIN

DIFFERENTIAL TRAVEL--- .001 MAX

OVERTRAVEL----- .005 MIN

**ELECTRICAL DATA**

CONTACT ARRANGEMENT  
SPDT

30 VOLTS DC RATING

	SEA LEVEL	50,000 FT
INDUCTIVE	1/2 AMP	1/2 AMP
RESISTIVE	1 AMP	1 AMP

MAXIMUM INRUSH 2 AMP

APPROVALS

KEMA, CE	1A, 250V ~ T85 1E4	CE
UL, CSA	1A, 125 VAC	UL, CSA

DESIGN UNITS: INCH

TOLERANCES UNLESS NOTED:

NO PLACE	X	±	
ONE PLACE	.X	±	0.030
TWO PLACE	.XX	±	0.015
THREE PLACE	.XXX	±	0.005
FOUR PLACE	.XXXX	±	
ANGLES		±	

THIRD ANGLE PROJECTION

DRAWN	VK	27 NOV 07
CHECK	RJ	27 NOV 07

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY

RASTER

**Honeywell**

TITLE: SWITCH - BASIC

SIZE	TYPE	DRAWING NAME	REV
B	I	11SM423-H2	4

SCALE	-	WEIGHT .006 LB	SHEET 1 OF 1
-------	---	----------------	--------------