



| |
|--------------------------|
| HONEYWELL PART NUMBER |
| 11SM423 |
| PRODUCT CODE TWY1150 |

| REV | DOCUMENT | CHANGED BY | CHECK |
|-----|----------|------------|-------|
| 11 | 0038104 | PK 23APR08 | ASD |



NOTES

- 1- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375±.002 CENTERS
- 2- TERMINALS ARE PLATED FOR SOLDERING
- 3- DEAD BREAK CONDITIONS:
 - A - MAX AMOUNT PERMISSIBLE ----- .0002 IN.
- 4 - MATING CONTACT SURFACES ARE 24K SOLID* GOLD OVERLAY

| | |
|-------------|--------|
| RELEASE NO. | PR-715 |
| REPLACES | - |

| CHARACTERISTICS | |
|---------------------|------------------|
| OPERATING FORCE | --- 3 1/2 OZ MAX |
| RELEASE FORCE | --- 1 OZ MIN |
| DIFFERENTIAL TRAVEL | --- .001 MAX |
| OVERTRAVEL | --- .005 MIN |

| ELECTRICAL DATA | | |
|-----------------------------|-----------|--------------------|
| CONTACT ARRANGEMENT SPDT | | |
| 30 VOLTS DC RATING | | |
| | SEA LEVEL | 50,000 FT |
| INDUCTIVE | 1/2 AMP | 1/2 AMP |
| RESISTIVE | 1 AMP | 1 AMP |
| MAXIMUM INRUSH 2 AMP | | |
| APPROVALS | KEMA, CE | 1A, 250V ~ T85 1E4 |
| | UL, CSA | 1A, 125 VAC |

| |
|--------------------------|
| DESIGN UNITS: INCH |
| TOLERANCES UNLESS NOTED: |
| NO PLACE X ± |
| ONE PLACE .X ± |
| TWO PLACE .XX ± |
| THREE PLACE .XXX ± |
| FOUR PLACE .XXXX ± |
| ANGLES ± |
| THIRD ANGLE PROJECTION |

| | | |
|--|----|-----------|
| DRAWN | VK | 27 NOV 07 |
| CHECK | RJ | 27 NOV 07 |
| THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL. | | |
| INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY | | |
| RASTER | | |

| | | | |
|--------------------------------|----------|----------------|--------------|
| Honeywell | | | |
| TITLE SWITCH - BASIC | | | |
| SIZE | TYPE | DRAWING NAME | REV |
| B | I | 11SM423 | 11 |
| SCALE | - | WEIGHT .006 LB | SHEET 1 OF 1 |