

Honeywell Sensing and Control

Search


[narrow your search](#)

Products

- Controls Monitoring and Lighting (354)
- Machine Safety (1726)
- Sensors (7016)
- Switches (9676)

Technology

- Control and Instrumentation (1063)
- Electromechanical (9237)
- Microstructure (2298)
- Optical/Infrared (1077)
- Thick Film (1764)
- More...

Need Help?

[Click here to contact us](#)

140-103LAG-RB1 Discrete Thermistors

[\(Home : Products\)](#)


Actual product appearance may vary.

140 Series, 2,54 mm [0.1 in] disc thermistor with leads, 10,000 Ohm resistance, ±10.0% tolerance, 25/85 BETA = 3974

[Sales & Service](#)
[Distributor Inventory](#)
[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Availability	Global
Resistance	10,000 Ohm
Tolerance	±10.0%
Accuracy	25 °C [77 °F]
Beta	3974
Operating Temperature	-60 °C to 125 °C [-76 °F to 257 °F]
Diameter	2,54 mm [0.10 in]
Termination Material	Tinned copper
Lead Length	38,1 mm [1.50 in]
Time Constant in Air	10.0 s
Dissipation Constant	3,0 m/W°C
Series Name	140