

Honeywell Sensing and Control

Search



BA-2RV32-P405

(Home : Products : Switches » MICRO SWITCH™ Basic Switches » Premium Large Basic Switches » BZ/BA/WA/YZ)

narrow your search

Products

- Controls Monitoring and Lighting (352)
- Machine Safety (1701)
- Sensors (6224)
- Switches (9749)
- Wireless (39)

Technology

- Control and Instrumentation (1052)
- Electromechanical (9301)
- Magnetic (541)
- Optical/Infrared (1042)
- Thick Film (1764)
- More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XYR6000™

[find out more](#)

white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

Need help?

[Click here to contact us](#)



Actual product appearance may vary.
[click here to download Hi-Res image](#)

BA Series Standard Basic Switch, Single Pole Double Throw Circuitry, 20 A at 250 Vac, Straight Lever Actuator, 0,28 N [1.0 oz] Operating Force, Screw Termination, Silver Contacts, UL, CSA, CE, ENEC, Rigid Lever

[Sales & Service](#)

[Distributor Inventory](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Switch Type	MICRO SWITCH™ Standard 25,4 mm H x 17,8 mm W x 50,8 mm L [1.0 in H x 0.7 in W x 2.0 in L]
Sealed	No
Ampere Rating	20 A
Circuitry	SPDT
Actuator	Straight Lever
Termination	Screw
Operating Temperature	-55 °C to 85 °C [-67 °F to 185 °F]
Voltage	250 Vac
Actuator Length	31,75 mm [1.25 in]
Contact Type	Silver
Operating Force (OF)	1,39 N [5.0 oz] max.
Release Force	0,28 N [1.0 oz] min.
Pretravel (PT)	7,87 mm [0.310 in] max.
Overtravel (OT)	0,76 mm [0.030 in] min.
Differential Travel (DT)	1,52 mm [0.060 in] max.
Operating Position (OP)	19,1 mm ±0,76 mm [0.75 in ± 0.03 in]
Free Position (FP)	26,97 mm [1.062 in] max.
Material	Plastic
Housing Material	General Purpose Phenolic
Agency Approvals and Standards	UL, CSA, CE, ENEC
Mounting Screw Size	3,53 mm [0.139 in]
Mounting Centers	25,4 mm [1 in]
Tightening Torque	0,33 N m [3.0 in lb]
Weight	28,6 g [0.063 lb]
Package Height	24,1 mm [0.95 in]
Package Width	17,5 mm [0.69 in]
Package Length	49,3 mm [1.94 in]
Comment	CE: 61058-1; UL: E12252; CSA: LR41370; Left side facing #8 screw with cupwasher, solder lug base
Availability	Global
UNSPSC Code	30211905
UNSPSC Commodity	30211905 Snap switches
Series Name	BZ/BA/WA/YZ

contacts

- Customer Service
- Technical Support
- Global Sales & Service
- View Site Demo
- Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

my links

- Login to iCOM
- Login to Rep/AD Portal
- Login to Digital University

News Center

HONEYWELL ANNOUNCES ADDITION TO RELIALIGN™ RESIDENTIAL DOOR INTERLOCK SWITCHES THAT FEATURE RUGGED, PLASTIC HOUSING

HONEYWELL RELEASES UNLIMITED POTENTIAL WITH NEW LIMITLESS™ WIRELESS SWITCHES

HONEYWELL'S XYR6000 WIRELESS POSITION SENSOR ENABLES MONITORING IN HAZARDOUS AREAS AND REMOTE LOCATIONS

MICRO SWITCH Anniversary site