

## Honeywell Sensing and Control

Search

### narrow your search

#### Products

- Controls Monitoring and Lighting (352)
- Machine Safety (1702)
- Sensors (6223)
- Switches (9750)
- Wireless (21)

#### Technology

- Capacitive (26)
- Electromechanical (9301)
- Microstructure (1486)
- NTC Thermistors (147)
- Thick Film (1764)
- More...

### new products

#### New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



[Wireless Web Site WGLA and WPMM XYR6000™](#)

[find out more](#)

### white papers

- ▶ [Wireless Switches Offer Unlimited Benefit](#)
- ▶ [Basic Switches Are Not Created Equal](#)
- ▶ [Applying Precision Switches](#)
- ▶ [Sensors for Medical Devices](#)
- ▶ [New Ways to Measure Torque](#)
- ▶ [Choosing Safety Switches](#)
- ▶ [Specifying Hour Meters](#)

### Need help?

[Click here to contact us](#)

### 1CPSA3 Cable Pull (Home : Products)



*Actual product appearance may vary.*

Series, Cable Pull Safety Switch, Cable, 1/2 NPT, Silver

[Sales & Service](#)

[Distributor Inventory](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

#### Product Specifications

Product Type	Cable Pull Safety Switch
Actuator	Cable, Maintained
Switch Type	3NC/1NO Direct Opening
Contact Material	Silver
Termination Type	1/2 NPT
Ampere Rating	50 mA to 10 A (Thermal)
Voltage	600 Vac and 250 Vdc max.
Housing Material	Zinc Die-Cast
Series Name	1CPS
Shock	15 G
Vibration	10 Hz to 500 Hz, 5 G
Sealing	IP67; NEMA 1, 4, 12, 13
CSA File #	LR57326
UL File #	E37138, E157416
Agency Approvals and Standards	UL, CE, CSA
Expected Mechanical Life	1 Million
Operating Temperature	-40 °C to 85 °C [-40 °F to 185 °F]
Availability	Global
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and Controls and Relays
Contact Block	Removable with Heavy Duty Wiring Receptacles
Indicator	None
Comment	Low Voltage Directive 73/23/EEC, as amended by directive 93/68/EEC. Machinery Directive 98/37/EEC only as the directives relate to the components being used in a safety function. EN60947-1, EN-60947-5-1, EN60947-5-5

### contacts

- ▶ [Customer Service](#)
- ▶ [Technical Support](#)
- ▶ [Global Sales & Service](#)
- ▶ [View Site Demo](#)
- ▶ [Site Comments?](#)

### meet dr. larry

**VIDEO - Dr. Larry Goldstein** explains our newest and best technologies.



- ▶ [Meet Dr. Larry](#)

### my links

- ▶ [Login to iCOM](#)
- ▶ [Login as Rep/AD](#)
- ▶ [Login as Guest](#)
- ▶ [Login to Digital University](#)

### News Center

- ▶ [HONEYWELL ANNOUNCES ADDITION TO RELIALIGN™ RESIDENTIAL DOOR INTERLOCK SWITCHES THAT FEATURE RUGGED, PLASTIC HOUSING](#)
- ▶ [HONEYWELL RELEASES UNLIMITED POTENTIAL WITH NEW LIMITLESS™ WIRELESS SWITCHES](#)
- ▶ [HONEYWELL'S XYR6000 WIRELESS POSITION SENSOR ENABLES MONITORING IN HAZARDOUS AREAS AND REMOTE LOCATIONS](#)

**MICRO SWITCH Anniversary site**