



HONEYWELL  
PART NUMBER  
1SM3-T  
PRODUCT CODE:  
JG-80305

REV	DOCUMENT	CHANGED BY	CHECK
11	0034444	JA 15OCT07	PSR

FOR FACTORY USE ONLY



- NOTE -
- 1- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ±.002 CENTERS
  - 2- TERMINALS ARE PLATED FOR SOLDERING
  - 3- SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

RELEASE NO.:

REPLACES

<b>CHARACTERISTICS</b> OPERATING FORCE-----3-5 OZ. RELEASE FORCE-----1 OZ. MIN. DIFFERENTIAL TRAVEL-----.004 MAX. OVERTRAVEL-----.005 MIN.	<b>ELECTRICAL DATA</b> CONTACT ARRANGEMENT SPDT 30 VOLTS DC RATING SEA LEVEL      50,000 FT INDUCTIVE      3 AMP      2.5 AMP RESISTIVE      5 AMP      5 AMP MAXIMUM INRUSH 24 AMP		DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE      X      ±      0.040 ONE PLACE      .X      ±      0.030 TWO PLACE      .XX      ±      0.015 THREE PLACE      .XXX      ±      0.005 FOUR PLACE      .XXXX      ±      0.0005 ANGLES      ±      2	DRAWN      JA      15OCT07 CHECK      PSR      15OCT07	<b>Honeywell</b> TITLE SWITCH-BASIC		
	APPROVALS KEMA, CE      5A, 250V ~ T85 1E4 UL, CSA      5A, 250 VAC	THIRD ANGLE PROJECTION 	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.	INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			
	RASTER			SCALE      -      WEIGHT .006 LB MAX      SHEET 1 OF 1			