

Honeywell Sensing and Control

Search

2CPSA1A1A
(Home : Products : Machine Safety » MICRO SWITCH™ Safety Switches » Cable Pull » 2CPS)

narrow your search

- Products**
- Controls Monitoring and Lighting (286)
 - Machine Safety (1727)
 - Sensors (6004)
 - Switches (9781)
 - Wireless (45)

- Technology**
- Control and Instrumentation (988)
 - Electromechanical (9307)
 - Magnetic (541)
 - Platinum thin film (56)
 - Thick Film (1409)
 - More...



2CPS Series, Cable Pull Safety Switch, Cable, Maintained Both Sides, 2NC/2NO Direct Opening (Switch 2, Left: 1NC/1NO; Switch 2, Right: 1NC/1NO), 1/2 NPT, Gold-plated Contacts, 24 Vdc Multi-cluster LED

Actual product appearance may vary.

[Sales & Service](#)

[Distributor Inventory](#)

Overview **Specs** Documentation Application Notes

Product Specifications

Product Type	Cable Pull Safety Switch
Actuator	Cable, Maintained Both Sides
Switch Type	2NC/2NO Direct Opening (Switch 1, Left: 1NC/1NO; Switch 2, Right: 1NC/1NO)
Contact Material	Gold-plated
Termination Type	1/2 NPT
Ampere Rating	10 uA to 50 mA Low Energy
Voltage	250 Vac and 60 Vdc max.
Housing Material	Zinc Die-Cast
Series Name	2CPS
Shock	15 G
Vibration	10 Hz to 500 Hz, 5 G
Sealing	IP67: NEMA 1, 4, 12, 13
CSA File #	LR57326
UL File #	E37138, E157416
Agency Approvals and Standards	UL, CE, CSA, SIL 3 capable
Expected Mechanical Life	1 Million
Operating Temperature	-40 °C to 85 °C [-40 °F to 185 °F]
Availability	Global
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and Controls and Relays
Contact Block	Mounted to Housing
Indicator	24 Vdc Red Multi-cluster LED
Comment	Low Voltage Directive 73/23/EEC, as amended by directive 93/68/EEC. Machinery Directive 98/37/EEC only as the directives relate to the components being used in a safety function. EN60947-1, EN-60947-5-1, EN60947-5-5

contacts

- ▶ Customer Service
- ▶ Technical Support
- ▶ Global Sales & Service
- ▶ View Site Demo
- ▶ Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



▶ Meet Dr. Larry

my links

- ▶ Login to iCOM
- ▶ Login to Rep/AD Portal
- ▶ Login to Digital University

News Center

- ▶ HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER
- ▶ HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION
- ▶ HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO
- ▶ HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION
- ▶ HONEYWELL INTRODUCES MICROPOWER OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT

MICRO SWITCH Anniversary site

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site WGLA and WPMM XYR6000™

[find out more](#)

white papers

- ▶ Wireless Switches Offer Unlimited Benefit
- ▶ Basic Switches Are Not Created Equal
- ▶ Applying Precision Switches
- ▶ Sensors for Medical Devices
- ▶ New Ways to Measure Torque
- ▶ Choosing Safety Switches
- ▶ Specifying Hour Meters

Need help?

[Click here to contact us](#)