



| | | |
|--|--|--|
| THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH | | THIRD ANGLE PROJECTION |
| CHARACTERISTICS | | SCALE 2 TO 1 |
| ELECTRICAL DATA | | DO NOT SCALE PRINT |
| CONTACT ARRANGEMENT | | UNLESS OTHERWISE SPECIFIED TOLERANCES ARE |
| D P D T | | ONE PLACE (.0) ± .030 |
| L181 | | TWO PLACE (.00) ± .015 |
| 10A 1/2HP 125, 250 OR 277 VAC | | THREE PLACE (.000) ± .005 |
| | | ANGLES ± 5° |
| | | WEIGHT |

NOTES

- 1 — BLACK PLASTIC CASE AND PLUNGER
- 2 — NOMINAL CUTOUT DIMENSION FOR PANELS BETWEEN .045 AND .100 SHOULD BE INTERPOLATED BETWEEN 1.445 AND 1.455
- 3 — PUSH TO OPERATE — MOMENTARY