

Honeywell Sensing and Control

Search

3450HR 04550008
(Home : Products : Sensors » Thermostats » 3450HR)

narrow your search

- Products**
- Controls
 - Monitoring and Lighting (286)
 - Machine Safety (1727)
 - Sensors (5910)
 - Switches (9781)
 - Wireless (45)
- Technology**
- Electromechanical (9307)
 - Magnetic (541)
 - Microstructure (1495)
 - Optical/Infrared (1042)
 - Thick Film (1409)
 - More...



3450HR Series Phenolic Automatic Reset Thermostats

Actual product appearance may vary.

[Sales & Service](#)

[Distributor Inventory](#)

Overview Specs Documentation Application Notes

Product Specifications

Functional Properties	Open on rise
Reset Type	Automatic
Amperage	15 A/10 A resistive max.
Voltage	120 Vac/240 Vac
Operating Temperature	0 °C to 150 °C [32 °F to 302 °F]
Environmental Exposure Range	-18 °C to 177 °C [0 °F to 350 °F]
Open Temperature	60.0 °C [140 °F]
Close Temperature	46.1 °C [115 °F]
Open Tolerance	2.8 °C [5 °F]
Close Tolerance	4.4 °C [8 °F]
Housing Material	Phenolic
Contact Material	Silver/nickel alloy
Agency Approvals and Standards	UL, CSA
Mounting	B201 fixed bracket
Series Name	3450HR

contacts

- ▶ Customer Service
- ▶ Technical Support
- ▶ Global Sales & Service
- ▶ View Site Demo
- ▶ Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



▶ Meet Dr. Larry

my links

- ▶ Login to iCOM
- ▶ Login to Rep/AD Portal
- ▶ Login to Digital University

News Center

- ▶ HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO
- ▶ HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION
- ▶ HONEYWELL INTRODUCES MICROPOWER OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT
- ▶ HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XYR6000™

[find out more](#)

white papers

- ▶ Wireless Switches Offer Unlimited Benefit
- ▶ Basic Switches Are Not Created Equal
- ▶ Applying Precision Switches
- ▶ Sensors for Medical Devices
- ▶ New Ways to Measure Torque
- ▶ Choosing Safety Switches
- ▶ Specifying Hour Meters

Need help?

[Click here to contact us](#)

MICRO SWITCH Anniversary site

