

Honeywell Sensing and Control

Search 

3455RG 81290064

(Home : Products : Sensors » Thermostats » 3455RG)

narrow your search

Products

- Controls Monitoring and Lighting (352)
- Machine Safety (1727)
- Sensors (5910)
- Switches (9781)
- Wireless (45)

Technology

- Capacitive (26)
- Control and Instrumentation (1054)
- Electromechanical (9307)
- Microstructure (1495)
- Thick Film (1409)
- More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XYR6000™

find out more 

white papers

- ▶ Wireless Switches Offer Unlimited Benefit
- ▶ Basic Switches Are Not Created Equal
- ▶ Applying Precision Switches
- ▶ Sensors for Medical Devices
- ▶ New Ways to Measure Torque
- ▶ Choosing Safety Switches
- ▶ Specifying Hour Meters

Need help?

Click here to contact us 



3455RG Series Phenolic Automatic Reset Thermostats

Actual product appearance may vary.

Sales & Service 

Distributor Inventory 

Overview Specs Documentation Application Notes

Product Specifications

Functional Properties	Open on rise
Reset Type	Automatic
Amperage	0.5 A
Voltage	250 Vac/50 Vdc
Operating Temperature	0 °C to 150 °C [32 °F to 302 °F]
Environmental Exposure Range	-18 °C to 177 °C [0 °F to 350 °F]
Open Temperature	51.7 °C [125 °F]
Close Temperature	37.8 °C [100 °F]
Open Tolerance	2.8 °C [5 °F]
Close Tolerance	3.9 °C [7 °F]
Dielectric Strength	MIL-STD-202, Method 301; 2000 Vac 60 Hz - Terminal to Case
Insulation Resistance	MIL-STD-202, Method 302; Cond. B - 500 MOhm - 500 Vdc applied
Contact Resistance	MIL-STD-202, Method 307; 0.050 Ohm
Housing Material	Phenolic
Contact Material	WE -1 gold alloy cross point
Agency Approvals and Standards	UL, CSA, VDE
Mounting	B205 airstream bracket
Series Name	3455RG

contacts

- ▶ Customer Service
- ▶ Technical Support
- ▶ Global Sales & Service
- ▶ View Site Demo
- ▶ Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



- ▶ Meet Dr. Larry

my links

- ▶ Login to iCOM
- ▶ Login to Rep/AD Portal
- ▶ Login to Digital University

News Center

- ▶ HONEYWELL INTRODUCES MICROPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT
- ▶ HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION
- ▶ HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO
- ▶ HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION

MICRO SWITCH Anniversary site



