


REPLACES
6AT29
 DRAWING NUMBER
M
 ISSUE
8
 RELEASE NO. SR 5210
 16 APR. 56
 CHECK CNT
 16 APR. 56
 CHECK J.S.S.
 4 APR. 59
 CHECK KAG
 14 FEB 86
 CHECK CO-68001
 20 JUL 90
 CHECK G.J.W.
 22 APR 02
 CHECK S.A.V.
 8 MAY 02
 3 APR. 56
 CHECK K.F.M.
 DRAWN
 RASTER
 74-98



- NOTES:
- 1 - UNIT INCLUDES (2) CATALOG LIST, ISMI BASIC SWITCH
 - 2 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
 - 3 - TERMINALS ARE PLATED FOR SOLDERING
 - ⚠ HARDWARE FURNISHED UNASSEMBLED WITH SWITCH OR IN PACKET 15PA312-AT PER MIL - PRF-8805
 - 5 - REPLACEMENT MOUNTING HARDWARE PACKET 15PA312-AT

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

ELECTRICAL DATA

SCALE FULL

CONTACT ARRANGEMENT

(2) S.P.D.T. (A)

250 VAC ————— 5 AMP

30 VOLTS DC RATING

INDUCTIVE — SEA LEVEL ——— 3 AMP

50,000 FT. ——— 2.5 AMP

RESISTIVE — SEA LEVEL ——— 5 AMP

50,000 FT. ——— 5 AMP

(B)

MAXIMUM INRUSH ————— 24 AMP

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) ±.030

TWO PLACE (.00) ±.015

THREE PLACE (.000) ±.008

ANGLES ±

WEIGHT .06 LB.