



MICRO SWITCH

FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL


FED. MFG. CODE 91929

ASSEMBLY- TOGGLE SWITCH

CATALOG LISTING

6AT6

RASTER
 FO-80376
 DRAWN
 O M W 10 MAY 66
 CHECK
 L S D 12 MAY '68
 CHECK
 20 JUL 90
 SAV
 8 JUL 87
 J A P
 CO-68001
 F
 8 JUL 87
 J A P
 CO-68001
 F
 14 FEB 86
 K A G
 CO-58771
 D
 5 MAY 82
 W J M
 50566-B
 C
 1 NOV 66
 W E G
 CO21979
 B
 10 MAY 66
 O M W
 CO15200
 A
 ISSUE 16
 DRAWING NUMBER
 M
 PAGE 1 OF 1
 6AT6
 REPLACES
 RELEASE NO.



- NOTES:
- 1- UNIT INCLUDES CAT. LIST. ISMIBASIC SWITCH
 - 2- TERMINALS ARE PLATED FOR SOLDERING
 - ³ HARDWARE FURNISHED ASSEMBLED WITH SWITCH OR IN PACKET PER MIL-PRF-8805

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

ELECTRICAL DATA

SCALE FULL

CONTACT ARRANGEMENT
S P D T

DO NOT SCALE PRINT

UNLESS OTHERWISE NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0)	± .030
TWO PLACE (.00)	± .015
THREE PLACE (.000)	± .005
ANGLES	±

WEIGHT .05 LB

250 VAC	5 AMP
30 VOLTS DC RATING	
INDUCTIVE	SEA LEVEL --- 3 AMP
	50,000 FT --- 2.5 AMP
RESISTIVE	SEA LEVEL --- 5 AMP
	50,000 FT --- 5 AMP
MAXIMUM INRUSH	24 AMP