


**DC Hour Meters - 85002 (/sensing.honeywell.com/product-page?pr\_id=)**



( Home (/) : Products (/products) : Controls and Monitoring : Monitors : DC Hour Meters : 85000 )

Distributor Inventory

Input part number for stock availability



Honeywell Hour Meter

85002\_highres\_photo (/honeywell-hour-meter-85002-highres.jpg)

85002\_lowres\_photo (/honeywell-hour-meter-85002-lowres.jpg)

[Sales & Service](#)

[Distributor Inventory](#)

**Narrow Your Search**

**Modify Your Search**

**Products**

Select Option

**Technology**

Select Option

**Industries Served**

Select Option

FEEDBACK

CHAT

[Overview](#)   [Specs](#)   [Documentation](#)   [Rich Media](#)

**Product Specifications**

Product Type	Quartz + Hour Meter
Mounting	2.27 Dia Cup
Voltage	10 Vdc to 32 Vdc
Bezel	Chrome
Hours	10K
Logo Top	Honeywell Quartz
Logo Bottom	Hours
Termination	1/4 inch Male Blade - Down
Lens	Glass
Temperature	-40 °C to 85 °C [-40 °F to 185 °F]
Quartz Accuracy	±0.02%
Vibration	20 g @ 10 Hz to 80Hz (SAE J1378)
Shock	55 g @ 9 msec to 13 msec (SAE J1378)
Alternator Load Dump	150 V
EMI	400 V @ 500 Hz
Sealing	IP66
Inductive Switching	Yes
Reverse Polarity	Yes
Number Size	3 mm [0.12 in]
Agency Approvals and Standards	UL (File number AU1774), CSA (File number LR42455-12)
Availability	Global
Comment	Hour Meter
Series Name	85000

**Product Search**

Product Type:

New Products Only

Industry: **All Industries** ▼

Entire Product Catalog

Search Term: **Start Here ...**

**Search**

### My Links

- [eCOM Login \(/index.php?ci\\_id=50629&la\\_id=1\)](/index.php?ci_id=50629&la_id=1)
- [Request Access to eCOM \(/ecom-access-request\)](/ecom-access-request)
- [Rep/AD Portal Login \(/index.php?ci\\_id=50606&la\\_id=1\)](/index.php?ci_id=50606&la_id=1)
- [Rep/AD Portal Access Request \(/index.php?ci\\_id=50630&la\\_id=1\)](/index.php?ci_id=50630&la_id=1)
- [Sample Request \(/samplerequest\)](/samplerequest)
- [Digital U - HWL Learning Hub Login \(/index.php?ci\\_id=50607&la\\_id=1\)](/index.php?ci_id=50607&la_id=1)
- [Limitless Microsite \(/index.php?ci\\_id=50631&la\\_id=1\)](/index.php?ci_id=50631&la_id=1)
- [YouTube \(/www.youtube.com/user/SensingAndControl\)](https://www.youtube.com/user/SensingAndControl)
- [Supplier Microsite \(/index.php?ci\\_id=44887&la\\_id=1\)](/index.php?ci_id=44887&la_id=1)

### Literature and Media

- [Data Sheets \(/white-paper-and-technical-data-sheets-library2\)](/white-paper-and-technical-data-sheets-library2)
- [Videos \(/videos\)](/videos)
- [Literature \(/literature\)](/literature)
- [Literature Request \(/index.php?ci\\_id=50636&la\\_id=1\)](/index.php?ci_id=50636&la_id=1)
- [White Papers \(/whitepapers\)](/whitepapers)
- [Application Notes \(/application-notes\)](/application-notes)
- [Application Demos \(/index.php?ci\\_id=141383&la\\_id=1\)](/index.php?ci_id=141383&la_id=1)
- [CAD Renderings \(/cad-renderings\)](/cad-renderings)

### Contacts

- [Customer Service \(/index.php?ci\\_id=50608&la\\_id=1\)](/index.php?ci_id=50608&la_id=1)
- [Technical Support \(/index.php?ci\\_id=50609&la\\_id=1\)](/index.php?ci_id=50609&la_id=1)
- [Global Sales & Service \(/index.php?ci\\_id=50610&la\\_id=1\)](/index.php?ci_id=50610&la_id=1)

[\(/contact\)](/contact)  
[\(/contact\)](/contact)

[Terms & Conditions \(/terms & conditions\)](/terms & conditions)

[Privacy Statement \(/index.php?ci\\_id=2589&la\\_id=1\)](/index.php?ci_id=2589&la_id=1)

[Site Map \(/site-map\)](/site-map)

FEEDBACK

CHAT