


DC Hour Meters - 85097 (/sensing.honeywell.com/product-page?pr_id=)



([Home \(/\)](#) : [Products \(/products\)](#) : [Controls and Monitoring](#) : [Monitors](#) : [DC Hour Meters](#) : 85000)

Distributor Inventory

Input part number for stock availability



Honeywell Hour Meter

85097_highres_photo (/honeywell-hour-meter-85097-02-highres.jpg)

85097_lowres_photo (/honeywell-hour-meter-85097-02-lowres.jpg)

[Sales & Service](#)

[Distributor Inventory](#)

[Overview](#) [Specs](#) [Documentation](#) [Rich Media](#)

Product Specifications	
Product Type	Quartz + Hour Meter
Mounting	3 Screw
Voltage	10 Vdc to 80 Vdc
Bezel	Black
Hours	10K
Logo Top	Honeywell Quartz
Logo Bottom	Hours
Termination	1/4 inch Male Blade - Down
Lens	Glass
Temperature	-40 °C to 85 °C [-40 °F to 185 °F]
Quartz Accuracy	±0.02%
Vibration	20 g @ 10 Hz to 80Hz (SAE J1378)
Shock	55 g @ 9 msec to 13 msec (SAE J1378)
Alternator Load Dump	150 V
EMI	400 V @ 500 Hz
Sealing	IP66
Inductive Switching	Yes
Reverse Polarity	Yes
Number Size	3 mm [0.12 in]
Agency Approvals and Standards	UL (File number AU1774), CSA (File number LR42455-12)
Availability	Global
Comment	Hour Meter
Series Name	85000

Narrow Your Search

Modify Your Search

Products

Select Option

Technology

Select Option

Industries Served

Select Option

FEEDBACK

CHAT

[\(/contact\)](#)

Product Search

Product Type:

New Products Only

Industry: All Industries ▼

Entire Product Catalog

Search Term: Start Here ...

Search

My Links

[eCOM Login \(/index.php?ci_id=50629&la_id=1\)](#)
[Request Access to eCOM \(/ecom-access-request\)](#)
[Rep/AD Portal Login \(/index.php?ci_id=50606&la_id=1\)](#)
[Rep/AD Portal Access Request \(/index.php?ci_id=50630&la_id=1\)](#)
[Sample Request \(/samplerequest\)](#)
[Digital U - HWL Learning Hub Login \(/index.php?ci_id=50607&la_id=1\)](#)
[Limitless Microsite \(/index.php?ci_id=50631&la_id=1\)](#)
[Supplier Microsite \(/index.php?ci_id=44887&la_id=1\)](#)
[SensingAndControl \(/www.youtube.com/user/SensingAndControl\)](#)

Literature and Media

[Data Sheets \(/white-paper-and-technical-data-sheets-library2\)](#)
[Videos \(/videos\)](#)
[Literature \(/literature\)](#)
[Literature Request \(/index.php?ci_id=50636&la_id=1\)](#)
[White Papers \(/whitepapers\)](#)
[Application Notes \(/application-notes\)](#)
[Application Demos \(/index.php?ci_id=141383&la_id=1\)](#)
[CAD Renderings \(/cad-renderings\)](#)

Contacts

[Customer Service \(/index.php?ci_id=50608&la_id=1\)](#)
[Technical Support \(/index.php?ci_id=50609&la_id=1\)](#)
[Global Sales & Service \(/index.php?ci_id=50610&la_id=1\)](#)

[\(/contact\)](#)
[\(/contact\)](#)

[Terms & Conditions \(/terms & conditions\)](#)

[Privacy Statement \(/index.php?ci_id=2589&la_id=1\)](#)

[Site Map \(/s](#)

FEEDBACK

CHAT

[\(/contact\)](#)