

## Honeywell Sensing and Control

Search

### narrow your search

#### Products

- Controls Monitoring and Lighting (352)
- Machine Safety (1701)
- Sensors (6224)
- Switches (9749)
- Wireless (39)

#### Technology

- Control and Instrumentation (1052)
- Electromechanical (9301)
- Magnetic (541)
- Optical/Infrared (1042)
- Thick Film (1764)
- More...

### new products

#### New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site  
WGLA and WPMM  
XYR6000™

[find out more](#)

### white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

#### Need help?

[Click here to contact us](#)

**914CE2-6**  
( Home : Products : Switches » MICRO SWITCH™ Limit Switches » MICRO SWITCH™ Medium-Duty Limit Switches » 914CE )



Actual product appearance may vary.

Miniature Enclosed Switches Series 914CE: Top Roller Plunger; 1NC 1NO SPDT Snap Action; 6 foot Cable

[Sales & Service](#)

[Distributor Inventory](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

#### Product Specifications

Availability	Global
Operating Force (OF)	11,8 N [2.65 lb] max.
Release Force	4,4 N [0.99 lb] max.
Pretravel (PT)	1,0 mm ±0,5 mm [0.04 in ±0.02 in]
Overtravel (OT)	3,0 mm [0.118 in] min.
Differential Travel (DT)	0,1 mm [0.004 in] max.
Product Type	MICRO SWITCH™ Miniature Limit Switches
Actuator	Top Roller Plunger
Lever Type	None
Circuitry	1NC 1NO SPDT Snap Action
Ampere Rating	5 A (Thermal)
Supply Voltage	240 Vac
Housing Material	Zinc Die-Cast
Termination Type	6 foot Cable
Series Name	914CE
Sealing	IP66, IP67, IP68; NEMA 1, 2, 3, 3R, 4, 6, 6P, 13
UL File #	E41859
Expected Mechanical Life	up to 10 Million
Operating Temperature	0 °C to 70 °C [35 °F to 160 °F]
Comment	Bottom Exit Cable
Agency Approvals and Standards	UL, CE, CSA, IEC947-5-1, EN60947-5-1
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Sealed	Industrial

### contacts

Customer Service  
Technical Support  
Global Sales & Service  
View Site Demo  
Site Comments?

### meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

### my links

Login to iCOM  
Login to Rep/AD Portal  
Login to Digital University

### News Center

HONEYWELL ANNOUNCES ADDITION TO RELIALIGN™ RESIDENTIAL DOOR INTERLOCK SWITCHES THAT FEATURE RUGGED, PLASTIC HOUSING

HONEYWELL RELEASES UNLIMITED POTENTIAL WITH NEW LIMITLESS™ WIRELESS SWITCHES

HONEYWELL'S XYR6000 WIRELESS POSITION SENSOR ENABLES MONITORING IN HAZARDOUS AREAS AND REMOTE LOCATIONS

### MICRO SWITCH Anniversary site