


MICRO SWITCH
a Honeywell Division


FED. MFG. CODE 91929

SWITCH-ENCLOSED

CATALOG LISTING
8LS1-L




CATALOG LISTING
8LS1-L
PAGE 1 OF 1
REPLACES
RELEASE NO. SR-13000
CHECK
REVISIONS
A CO-76997
GJW 13 APR 95
B C094494
JAF 22 MAR 99
CHECK
8 MAY 95
JAF
CHECK
13 APR 95
DRAWN
GJW



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

THIRD ANGLE PROJECTION



SCALE 1/2 TO 1

DO NOT SCALE PRINT

CHARACTERISTICS
OPERATING FORCE ----- 5 OZ MAX
FORCE AT 2.0 ----- 10 OZ MAX
SWITCH - BASIC REPLACEMENT ----- 2MNII-L

ELECTRICAL DATA
CONTACT ARRANGEMENT (SEE CIRCUIT DIAGRAM)
L128 10A 125, 250 OR 480 VAC 1/4HP 125 VAC, 1/2HP 250 VAC 0.8A 125 VDC, 0.4A 250 VDC

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
ONE PLACE	(.0) ±.030
TWO PLACE	(.00) ±.015
THREE PLACE	(.000) ±.005
ANGLES	±
WEIGHT	

NOTE
 SEAL FURNISHED BY USER

