



HONEYWELL PART NUMBER
91SX49
PRODUCT CODE VDQ9131

REV	DOCUMENT	CHANGED BY	CHECK
3	0038450	PK 03JUN08	ASD



NOTES
 MOUNTING HOLES WILL ACCEPT PINS OR SCREW OF $\phi .087$ MAX ON $.188 \pm .002$ CENTERS
 2 - TERMINALS ARE PLATED FOR SOLDERING

RELEASE NO.	PR-21572
REPLACES	X96327-SX

CHARACTERISTICS	
OPERATING FORCE	5 OZ MAX
RELEASE FORCE	1 OZ MIN
DIFFERENTIAL TRAVEL	.005 MAX
OVERTRAVEL	.004 MIN

ELECTRICAL DATA			
CONTACT ARRANGEMENT SPDT			
	28 VOLTS DC RATING		115 VOLTS AC, 60 CPS
	SEA LEVEL	50,000 FT	SEA LEVEL
INDUCTIVE	4 AMP	2.5 AMP	7 AMP
RESISTIVE	7 AMP	4 AMP	7 AMP
LAMP	2.5 AMP	2.5 AMP	2 AMP

DESIGN UNITS:	INCH
TOLERANCES UNLESS NOTED:	
NO PLACE	X ±
ONE PLACE	.X ±
TWO PLACE	.XX ±
THREE PLACE	.XXX ±
FOUR PLACE	.XXXX ±
ANGLES	±

DRAWN	SPK	04MAR08
CHECK	RJ	04MAR08
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		

Honeywell			
TITLE SWITCH - BASIC			
SIZE	TYPE	DRAWING NAME	REV
B	I	91SX49	3
SCALE	-	WEIGHT: .003 LB MAX	SHEET 1 OF 1