



MICRO SWITCH

FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BZ-2RW82113T

M BZ-2RW82113T

PAGE 1 OF 1

DRAWING NUMBER

ISSUE 4

REPLACES

RELEASE NO. SR 11678

CHECK

15 JULY 64

CHECK

15 JULY 64

CHECK


15 JULY 64

CHECK

13 JUL 64

CHECK

13 JUL 64



6-32UNC X .218 REF BINDER HEAD TERMINAL SCREW AND LOCKWASHER (SEMS) (3)

REVISIONS

A	CO-69351-D	JWB	18 JUL 91
B	CO-77589	TSM	29 MAR 94
C	CO93346	DLT	16 SEP 98

FORMTEK

FC-90378

DRAWN

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE ----- 3 1/2 OZ MAX	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE ----- 3/4 OZ MIN	UNDERWRITERS' LAB. INC. LISTED RATINGS -L96- 15A-125, 250, OR 480 VAC 1/2 A-125 VDC; 1/4 A-250 VDC 1/8 HP-125 VAC; 1/4 HP-250 VAC	UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES TOLERANCES ARE: ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±
DIFFERENTIAL TRAVEL ----- .004-.040	-L288- -L299- -L306- 16A 250V ~ T85 5E4	WEIGHT .076 LB
OVERTRAVEL ----- .124 MIN		