



HONEYWELL

1LS9

See full Datasheet below...

onlinecomponents.com

THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS

BUY NOW



MASTERTM
ELECTRONICS

BUY NOW

masterelectronics.com & onlinecomponents.com
are **authorized** e-commerce distributors
of electronic components.

 [→](#)

narrow your search

Products

- Controls Monitoring and Lighting (354)
- Machine Safety (1726)
- Sensors (7072)
- Switches (9814)

Technology

- Control and Instrumentation (1063)
- Electromechanical (9357)
- Microstructure (2329)
- Optical/Infrared (1077)
- Thick Film (1764)
- More...

Need Help?

Click here to contact us [→](#)

1LS9 MICRO SWITCH™ Medium-Duty Limit Switches

(Home : Products)



Actual product appearance may vary.

Enclosed Switches Series LS: Side Rotary - Lever Not Included; 1NC 1NO SPDT Snap Action, Double Break; 0.5 in - 14NPT conduit; Compact/Non-Plug-in

[Sales & Service](#) [→](#)

[Distributor Inventory](#) [→](#)

[Overview](#)

[Specs](#)

[Documentation](#)

[Application Notes](#)

Description

MICRO SWITCH™ compact LS and plug-in 200LS limit switches have a long record of successful performance in industrial applications. The MICRO SWITCH™ LS fits in many places too small for any other fully adjustable limit switch. The MICRO SWITCH™ 200LS switches are the original plug-in concept for reducing downtime by making changeover simple and fast.

Features

Features

- Mode of operation is field adjustable
- NEMA 1, 3, 4, 6, and 13
- Wide choice of heads and actuators
- Variety of operating characteristics
- Captive screws
- UL and CSA approved parts available

Potential Applications

Potential Applications

- Machine tools
- Conveyors
- Material handling
- Metal fabrication equipment
- Lift trucks