

LSYAC5KP-FP

(Home : Products : Switches : MICRO SWITCH™ Limit Switches) -Duty Limit Switches : HDLS - Fully Potted)

- New Products
- Products
- Warranty Information



Fully Potted Limit Switches HDLS Non Plug-in; Side Rotary; 1NC 1NO SPDT Snap Action; 12-foot Cable

Actual product appearance may vary.

- Sales & Service
- Distributor Inventory

- Overview
- Specs**
- Documentation
- Application Notes

Product Specifications

Availability	Global
Operating Force (OF)	0,45 N m [4 in lb] max.
Pretravel (PT)	15° max.
Overtravel (OT)	60° min.
Differential Travel (DT)	5° max.
Product Type	MICRO SWITCH™ Fully Potted Heavy-Duty Limit Switches
Actuator	Side Rotary
Lever Type	Lever Not Included - Reference Lever Required Accessory
Circuitry	1NC 1NO SPDT Snap Action, Double Break
Ampere Rating	10 A (Thermal)
Supply Voltage	600 Vac and 250 Vdc max.
Housing Material	Zinc Die-Cast
Termination Type	12 foot Cable
Housing Type	HDLS Non Plug-in
Series Name	HDLS - Fully Potted
Sealing	NEVA 1, 3, 4, 6, 6P, 12, 13
UL File #	E37138
Operating Temperature	-12 °C to 105 °C [10 °F to 221 °F]
Comment	120 Vac Neon Indicator
Agency Approvals and Standards	UL, CE, CSA, CCC, EN60947-1, EN60947-5-1
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Sealed	Industrial

Distributor Inventory

Input part number for stock availability

Narrow Your Search

Modify Your Search

Products

Select Option

Technology

Select Option

Industries Served

Select Option

Product Search

Product Type: All Product Types

Industry: All Industries

Search Term: Start Here ...

New Products Only

Entire Product Catalog

Search

My Links

- > eCOM Login
- > Request Access to eCOM
- > Rep/AD Portal Login
- > Rep/AD Portal Access Request
- > Sample Request
- > Digital University Login
- > Digital University Access Request
- > Limitless Microsite
- > Supplier Microsite

Literature and Media

- > Data Sheets
- > Videos
- > Literature
- > Literature Request
- > White Papers
- > Application Notes
- > Application Demos
- > CAD Renderings

Contacts

- > Customer Service
- > Technical Support
- > Global Sales & Service
- > Website Feedback



[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)