

# 28000

[Products](#) > [Controls and Monitors](#) > [Operator Controls](#) > [Hour Meters](#) > [ac Hour Meters](#) > [28100 Series](#) > **28000**

## Overview

Honeywell Standard ac Hour Meter, rectangle opening, retainer mount, 0.25 in bent blade termination, 100K hours, 108 Vac to 132 Vac operating voltage, 120 V, 60 Hz, faceplate:  
[View More](#)



## Technical Specifications

Product Type	Standard ac	Function	Hour Meter
Appearance	Rectangle	Mounting	Retainer
Voltage	108 Vac to 132 Vac	Volts ac	120 Vac
Frequency	60 Hz	Hours	100K
Logo Top	Hour Glass	Logo Bottom	Hours 1/10

[View More](#)

View documents in: English ▾

## Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
True Time Stamp - Hour Meters	Case Study	English	345KB
Hour Meters Line Guide	Product Line Guide	English	571KB
Industrial Product Line Card	Line Card/Selection Chart	English	571KB
Sensors and Switches for Potential Medical Applications	Application Note	English	374KB

[View More](#)

## Applications

- Control panels
- Medical applications

- [view all 28000 literature](#)
- [view distributor inventory](#)
- [sample request](#)
- [email support](#)
- [get support](#)
- [email sales](#)
- [find a distributor](#)
- [email this page](#)

### NAVIGATION LINKS

- [HOME PAGE](#)
- [PRODUCTS](#)
- [DISTRIBUTOR INVENTORY](#)
- [INDUSTRIES](#)
- [SUPPORT](#)

### DISTRIBUTOR LINKS

- [ECOM LOGIN](#)
- [LEARN CENTER](#)
- [REQUEST ACCESS TO ECOM](#)
- [SALES/AD PORTAL LOGIN](#)
- [SALES/AD PORTAL ACCESS REQUEST](#)

### LANGUAGE

English ▾

### SOCIAL MEDIA



### SITE INFORMATION

[NEWS & EVENTS](#)

[ABOUT US](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

[COPYRIGHT © 2018 HONEYWELL  
INTERNATIONAL INC.](#)