

- PRODUCTS ▾
- DISTRIBUTOR INVENTORY
- INDUSTRIES ▾
- SUPPORT ▾
- NEWS & EVENTS ▾
- ABOUT US ▾

3100U 00031440

[Products](#) > [Sensors](#) > [Humidity, Thermal & Flexible Heater Products](#) > [Thermostats/Thermal Switches](#) > [Precision](#) > [Preconfigured Redi-Temp](#) > [3100U Series](#) > **3100U 00031440**

Overview

3100 Series Hermetic Thermostats.

The 3100 Series consists of a single pole, single throw switch activated by a snap-action bimetal disc. Temperature of



[View More](#)

Technical Specifications

Functional Properties	Open on rise	Reset Type	Automatic
Operating Temperature	-29 °C to 260 °C [-20 °F to 500 °F]	Amperage	3 A resistive max.
Voltage	120 Vac	Open Temperature	54.4 °C [130 °F]
Open Tolerance	2.8 °C [5 °F]	Close Temperature	43.3 °C [110 °F]
Close Tolerance	2.8 °C [5 °F]	Environmental Exposure Range	-62 °C to 288 °C [-80 °F to 550 °F]

[View More](#)

View documents in:

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
Precision and High Reliability Thermostats	Datasheet	--	4MB
Thermostats Line Guide	Product Line Guide	English	444KB
Thermal Sensors	Product Range Guide	English	2MB

Product Features

- Hermetically sealed
- Tight tolerances
- Tight differentials

Applications

- Computers
- Medical electronics
- Power supplies
- Industrial controls
- Test equipment
- Infotech

- view all 3100U 00031440 literature
- view distributor inventory
- sample request
- email support
- get support
- email sales
- find a distributor
- email this page

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)


[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

English 

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

[COPYRIGHT © 2018 HONEYWELL INTERNATIONAL INC.](#)