

- [PRODUCTS ▾](#)
- [DISTRIBUTOR INVENTORY](#)
- [INDUSTRIES ▾](#)
- [SUPPORT ▾](#)
- [NEWS & EVENTS ▾](#)
- [ABOUT US ▾](#)

1TL1-3G

[Products](#) > [Switches](#) > [Toggle Switches](#) > [TL Series](#) > **1TL1-3G**

Overview

MICRO SWITCH TL Series Toggle Switch, 1 pole, 2 position, Screw terminal, Locking Lever, Military Part Number MS24658-23G...

[View More](#)



- [view all 1TL1-3G literature](#)
- [view distributor inventory](#)
- [sample request](#)
- [email support](#)
- [get support](#)
- [email sales](#)
- [find a distributor](#)
- [email this page](#)

Technical Specifications

Series Name	TL
Ampere/Voltage Range (Resistive Load)	0.5 A to 20 A at 0.5 Vdc to 28 Vdc 0.75 A at 115 Vdc 0.5 A to 15 A at 0.5 Vac to 277 Vac 0.5 A at 250 Vdc
Action	2 position
Mounting	Bushing 15/32 in
MIL Spec. Number	MS24658-23G

Product Type	MICRO SWITCH Toggle Switch
Circuitry	SPDT
Circuitry/Operating action	 ON ON
Termination	Screw
Lever Type	Locking

[View More](#)

View documents in:

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
1TL1-3G highres photo	Photo	English	2MB
1TL1-3G lowres photo	Photo	English	212KB
MICRO SWITCH TL Series Military-Grade Toggle Switches	Datasheet	English	2MB
Sensors and Switches in Oil Rig Applications	Application Note	English	7MB

[View More](#)

Product Features

- Qualified to MIL-DTL-3950
- Environment-proof sealing
- 1,2, and 4 pole circuitry
- Standard and pull-to-unlock levers
- 2 and 3 position, maintained and momentary toggle action
- Temperature range: -65 °C to 71 °C [-85 °F to 160 °F]

- Completely sealed switching chamber
- Step-design case provides added space between terminals to help prevent shorting
- UL recognized, CSA certified
- CE approved

Applications

- Industrial machinery and equipment
- Military and commercial aviation
- Construction equipment
- Test instruments
- Agricultural machinery
- Process control
- Medical instrumentation

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)


[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

English 

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.