

- PRODUCTS ▾
- DISTRIBUTOR INVENTORY
- INDUSTRIES ▾
- SUPPORT ▾
- NEWS & EVENTS ▾
- ABOUT US ▾

V15T16-CZ300A06-K

[Products](#) > [Switches](#) > [Basic Switches](#) > [General Purpose Basic Switches](#) > [V15 Series](#) > [V15T16-CZ300A06-K](#)

Overview

MICRO SWITCH V15 Series Standard Basic Switch, 16 A, long roller lever, 6,35 mm x 0,80 mm quick connect terminals, SPDT, 300 gf [2,94 N]. ...

[View More](#)







Technical Specifications

Switch Type	MICRO SWITCH Standard 15,9 mm H x 10,30 mm W x 27,80 mm L [0.63 in H x 0.41 in W x 1.09 in L]	Ampere Rating	16 A
Sealed	No	Circuitry	SPDT
Actuator	Long Roller Lever	Termination	Quick Connect
Operating Temperature	-25 °C to 125 °C [-13 °F to 257 °F]	Voltage	125 Vac/250 Vac
Actuator Length	59,5 mm [2.34 in]	Contact Type	Silver Cadmium Oxide

[View More](#)

View documents in:

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
 V15T16-CZ300A06-K highres photo	Photo	English	1MB
 V15T16-CZ300A06-K lowres photo	Photo	English	124KB
 MICRO SWITCH V15 Series Standard Basic Switches	Datasheet	English	2MB
 Sensors and Switches in Sanitary Valves	Application Note	English	430KB


[View More](#)

Product Features

Standard V-Basic Switch Features

- Best suited for lower cost-of-failure applications
- Designed from 10K to 50K operations at a full load or 5M for mechanical life
- World-wide package size acceptance
- Current rating ranges of 10 A and 26 A
- UL/CSA, cUL, ENEC, and CQC approvals

 [view all V15T16-CZ300A06-K literature](#)


 [view distributor inventory](#)

 [sample request](#)

 [email support](#)

 [get support](#)

 [email sales](#)

 [find a distributor](#)

 [email this page](#)

Applications

- Appliance
- Gaming
- Vending machines
- Water heaters
- Industrial controls

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)


[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

English 

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.