## Honeywell

### **Honeywell Sensing and Control**

Order Product and **Get Support** 

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

62NT1-8-NH

Actual product appearance may vary.

#### **Features**

Completely sealed switching chamber NEMA 3, 3R, 4, and 13 UL recognized, File E12252, Vol. 1, Section 44 CSA certified, File LR4442 CE approved

# **Potential Applications**

off feature, 2 pole step base, 2

position, Screw terminal, Standard

### Aerial lifts, scissor lifts, truck mounted tele-handlers, and cranes Construction equipment Agriculture equipment Material-handling equipment Factory-floor control units

NT Series Toggle Switch, Panel stand -

Machine tool equipment manufacturers

Login to iCOM Login as Rep/AD Login as Guest Login to Digital University

Keyword Search

My Links

Search for product and support information.

All Sensing and Contro

### Product Search

Part number search:

Use (\*) to expand search

**Specification Search** 

### Description

MICRO SWITCH™ NT Series toggle switches meet the need for a rugged, cost effective toggle switch. Quality construction features include a seal between the toggle lever and bushing, and between the cover and case. These switches can be used where panels are subject to splashes, hosedowns, or outdoor environments. The "Easy Start" threaded bushing enables quick alignment of mounting nut to decrease the chance of cross threading. The panel standoff with O-ring feature available on some listings, eliminates the need for behind he-panel hardware, provides uniform panel height, and provides a panel to cover seal.

Home> Products > MICRO SWITCH<sup>™</sup> Toggle Switches > NT > Product Page

Lever

Supporting Documentation     Accessory: Lever   Terminal     Sleeve   Identification     Panel Cutout   Accessory: Nuts     Product Specifications	
Circuitry/Operating action	
	Keyway Opposite Momentary Keyway Position Position 1 2 3 1 2 3
Product Type	6 5 4 6 5 4   MICRO SWITCH™ Toggle Switch
Ampere/Voltage Range (Resistive Load)	0.5 A to 10 A at 0.5 Vac to 277 Vac,0.75 A at 115 Vdc,0.5 A at 250 Vdc,0.5 A to 18 A at 0.5 Vdc to 28 Vdc
Circuitry	DPDT
Action	2 position
Mounting	Bushing 15/32 in
Termination	Screw
Lever Type	Standard
UL/CSA Rating Code	L192: 10 A - 125, 250, 277 Vac; 1/4 Hp - 125 Vac; 1/2 Hp - 250, 277 Vac; 3 A - 125 Vac "L"
Comment	Panel stand - off feature; Thermoplastic case; No hardware
Availability	Global
UNSPSC Code	30211908
UNSPSC Commodity	30211908 Toggle switches
Series Name	NT

Terms & Conditions | Privacy Statement | Site Map