

78146

[Products](#) > [Switches](#) > [Pressure Switches](#) > [Standard Pressure Switches](#) > [5000 Series](#) > **78146**

Overview

5000 Series pressure switch with standard terminal

These switches sense a change in the pressure, opening or closing an electrical circuit when the designated set point is reached. Honeywell S&C offers an impressive line of standard products, but our engineering expertise and understanding afford us the ability to modify existing parts or create an original component per a customer's specifications.



Technical Specifications

Operating Pressure	250 psi	Product Type	Pressure Switch
Connector(s)	1/8-27 NPT	Contact Setting Range	25 psi to 50 psi, ±5 psi
Standard Factory Set Points	30 psi, 35 psi, 40 psi, & 42 psi	Electrical Termination	#8-32 screw
Circuitry	NO	Contact(s)	Silver alloy, gold plated
Proof Pressure	500 psi	Burst Pressure	1250 psi

[View More](#)

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
HP, HE, MH, ME, LP, and LE Series Pressure Switches Datasheet	Datasheet	English	3MB
Series 5000 Extended Duty Pressure Switch Datasheet	Datasheet	English	120KB
Application Note: Honeywell Pressure Switches, HP-HE-ME-LP-LE Series	Application Note	English	1MB
Sensors and Switches in Mobile Cranes	Application Note	English	194KB

[View More](#)

Product Features

- Stands up to extended duty applications
- Factory set, capable of field adjustment
- Direct acting blade - gold-plated contacts
- No dead band
- Kapton diaphragm for compatibility with a variety of fluids
- Various electrical connections and terminations
- Optional rubber boot

- [view distributor inventory](#)
- [sample request](#)
- [email technical support](#)
- [start a chat we're online](#)
- [get support](#)
- [email sales](#)
- [find a distributor](#)
- [email this page](#)

Applications

- Engine transmission
- Hydraulics and brakes
- Power steering
- Fuel pressure
- ABS brakes
- Cruise control
- Oxygen concentrators
- Dental air
- Embalming equipment
- Generators/compressors
- Pool/spa water pressure

NAVIGATION LINKS

[HOME](#)

[PRODUCTS](#)

[INDUSTRIES](#)

[CONTACT US](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[DIGITAL U-HML](#)

[ECOM LOGIN](#)

[REQUEST ACCESS TO ECOM](#)

[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[LEARNING HUB LOGIN](#)

LANGUAGE

English 

SITE INFORMATION

[PRIVACY STATEMENT](#)

[TERMS & CONDITIONS](#)

This site uses cookies to simplify and improve your usage and experience of this website. Cookies are small text files stored on the device you are using to access this website. If you ignore this message and continue without changing your browser settings, we will assume that you are consenting to our use of cookies. For further information on our use of cookies, please see [Privacy Statement](#).

[Don't show this message again](#)