

- PRODUCTS ▾
- DISTRIBUTOR INVENTORY
- INDUSTRIES ▾
- SUPPORT ▾
- NEWS & EVENTS ▾
- ABOUT US ▾

# BZ-2RN784

[Products](#) > [Switches](#) > [Basic Switches](#) > [Premium Large Basic Switches](#) > [BZ Series](#) > [BZ-2RN784](#)

## Overview

MICRO SWITCH BZ Series Premium Large Basic Switch, Single Pole Double Throw Circuitry, 15 A at 250 Vac, Overtravel Plunger Actuator, 2,5 N - 3.61 N [9 oz - 13 oz] Operating Force

[View More](#)



## Technical Specifications

Switch Type	MICRO SWITCH Standard 25,4 mm H x 17,8 mm W x 50,8 mm L [1.0 in H x 0.7 in W x 2.0 in L]	Ampere Rating	15 A
Sealed	No	Circuitry	SPDT
Actuator	Overtravel Plunger	Termination	Screw
Operating Temperature	-55 °C to 85 °C [-67 °F to 185 °F]	Voltage	250 Vac
Contact Type	Silver	Operating Force (OF)	2,5 N to 3,61 N [9.0 oz to 13.0 oz]

[View More](#)

View documents in:

## Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
BZ-2RN784 highres photo	Photo	English	1MB
BZ-2RN784 lowres photo	Photo	English	59KB
MICRO SWITCH BZ/BA/BM/BE & 6AS Series Premium Large Snap-Action Switches	Datasheet	English	2MB
Oil and Gas Brochure	Brochure	English	4MB

[View More](#)

## Product Features

- Accepted world-wide standard "Large Basic" switch
- Low operating force and differential travel
- Long mechanical life up to 20,000,000 cycles at 95% survival
- Elongated mounting hole for easier, more accurate mounting
- Current rating ranges from 15 A to 25 A
- Choice of actuation, termination and operating characteristics

- [view all BZ-2RN784 literature](#)
- [view distributor inventory](#)
- [sample request](#)
- [email support](#)
- [get support](#)
- [email sales](#)
- [find a distributor](#)
- [email this page](#)

## Applications

---

- Irrigation systems
- Semi-trailer trucks
- Timing devices
- Office equipment
- Test instruments
- Medical/dental equipment
- HVAC equipment
- Manually operated devices
- Valves

### NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

### DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)


[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

### LANGUAGE

English 

### SOCIAL MEDIA



### SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL  
INTERNATIONAL INC.